
Document <i>Documento</i>	Firmware upgrade history <i>Storico aggiornamenti Firmware</i>
Model <i>Modello</i>	SYNSTAR 270/T
Code <i>Articolo</i>	8032400
Firmware version <i>Versione firmware</i>	11
Issue date <i>Data di rilascio</i>	27/09/2022

ITALIANO	2
ENGLISH	3

ITALIANO

Aggiornamenti Firmware rel. 11

- Nuova curva:
 - Rutile E71T1 1.2mm 100%CO2 short

Aggiornamenti Firmware rel. 10

- Modifiche interne
- Nuova curva:
 - Rutile E71T1 1.2mm Ar18%CO2 short

Aggiornamenti Firmware rel. 09

- Modifiche interne

Aggiornamenti Firmware rel. 08

- Modifiche interne

Aggiornamenti Firmware rel. 07

- Aggiunte curve sinergiche:
 - AlSiCu 1.2mm 100%Ar (SHORT, PULSE) (omologato Tesla)
 - X96 0.8mm (omologazione Honda) senza opzione

Aggiornamenti Firmware rel. 06

- Aggiunte curve sinergiche:
 - AlSiCu 1.2mm 100%Ar (SHORT, PULSE)

Aggiornamenti Firmware rel. 05

- Aggiunte funzioni:
 - 3L (tre livelli)
 - HSA (hot-start automatico)
 - CSA (corrente di cratere automatico)
- Disabilitato gruppo raffreddamento con la torcia push-pull inserita

Aggiornamenti Firmware rel. 04

- Aggiunta voce *Information* nel menù utente

Aggiornamenti Firmware rel. 03

- Risolto problema nella selezione della curva CuSi3 1.0 mm 100%Ar

Aggiornamenti Firmware rel. 02

- Aggiunte curve sinergiche:
 - Fe SG2 (0.6/0.8/ 0.9/1.0/1.2 mm) Ar+25%CO₂
 - SS 308L 0.9mm Ar+2%CO₂
 - AlMg5 0.9mm 100%Ar
 - AlMg12 0.9mm 100%Ar
 - CuSi3 0.9mm 100%Ar

ENGLISH

Updates Firmware rel. 11

- New synergic curve:
 - Rutile E71T1 1.2mm 100%CO₂ short

Updates Firmware rel. 10

- Internal improvements
- New synergic curve:
 - Rutile E71T1 1.2mm Ar18%CO₂ short

Updates Firmware rel. 09

- Internal improvements

Updates Firmware rel. 08

- Synergic programs updates

Updates Firmware rel. 07

- New synergic programs:
 - AlSiCu 1.2mm 100%Ar (SHORT, PULSE) (Tesla approval)
 - X96 0.8mm (Honda approval) now without option

Updates Firmware rel. 06

- New synergic programs:
 - AlSiCu 1.2mm 100%Ar (SHORT, PULSE)

Updates Firmware rel. 05

- Added functions:
 - 3L (three-levels)
 - HSA (automatic hot-start)
 - CSA (automatic crater-filler)
- Water unit disabled when the push-pull torch is connected

Updates Firmware rel. 04

- Added *Information* entry in the user menu

Updates Firmware rel. 03

- Fixed the problem about a synergic program CuSi3 1.0 mm 100%Ar

Updates Firmware rel. 02

- New synergic programs:
 - Fe SG2 (0.6/0.8/ 0.9/1.0/1.2 mm) Ar+25%CO₂
 - SS 308L 0.9mm Ar+2%CO₂
 - AlMg5 0.9mm 100%Ar
 - AlMg12 0.9mm 100%Ar
 - CuSi3 0.9mm 100%Ar